

MOTIP Removable Coating

Technical Information



Give details of your car a new look with a removable coating on parts such as rims and the logo emblem of your car with MOTIP Removable Coating. Remove the coating again easily by pulling off the created film. Suitable to treat smooth, non-absorbing surfaces, like blank metal, aluminium, glass and surfaces treated with 2K lacquers. MOTIP Removable Coating is oversprayable but not suitable for surfaces treated with 1K lacquer systems.

Ord.-no: 04301, 04302, 04304, 04303, 04305, 04306, 04307, 04308, 04309, 04310

Quality & properties

Resistant to chemicals and weather influences
Good filling property
Fast drying
360° valve

Physical & chemical data

Base: Synthetic rubber

Colourname:

- black
- carbon
- white
- green
- orange
- no colour
- blue
- red
- fluor yellow

Smell: Characteristic

Degree of gloss:

- mat, 10 ±2
- high gloss, >85

Efficiency: 500 ML – 0.4 m²

Dust dry: 20 - 40 min

Dry to touch: 30 min

Completely dry: 1 h

Surfaces: Metal, aluminium, glass, paintable hard plastics

Minimum Working Temperature: 10 °C

Maximum Working Temperature: 25 °C

Flash point: n.a.

Temperature resistance: 100 °C

Storage stability: 10 m

Content: 500 ML

How to use

Before use, carefully read the directions on the packaging and act accordingly.

Pre Treatment: Clean the surface, do not sand. The surface should be clean, dry and free of grease. Do not apply any primer.

The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 10 to 25°C at a relative humidity of <65%.

Before use, shake the aerosol for 3 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimetre.

Apply at least 5 layers removable lacquer, with an interval of 5 minutes. To avoid cracking of the film when removing this, apply an extra layer at critical spots (corners and edges).

The drying time depends on the ambient temperature, the humidity of the air and the thickness of the lacquer applied.

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

As of August 4, 2025 – This release replaces all eventually earlier issued versions.